



# LABFACILITY

TEMPERATURE & PROCESS TECHNOLOGY

## **ANSI Mineralisiertes Thermoelement mit Gewindetopf und 100 mm PFA-isoliertem doppelt verdrilltem ANSI-Kabel - Typ K - SS310 Mantel - 6,0 mm x 1000 mm**



Labfacility are the UK's leading manufacturer of Temperature Sensors, Thermocouple Connectors and associated Temperature Instrumentation and stockings of Thermocouple Cables. The Company has been trading since 1971 and is ISO9001 accredited.

**Mssen Sie Ihren Temperatursensor kalibrieren?**

Labfacility ist auf ISO17025 (UKAS)-Kalibrierstandards rckfhrbar und bietet die Wahl zwischen einer 3- oder 5-Punkt-rckfhrbaren Kalibrierung mit unserer hauseigenen Kalibriereinrichtung.

**Bitte beachten Sie, dass Sie bezglich der Lieferinformationen kontaktiert werden, wenn Sie Ihrer Bestellung eine Kalibrierungsoption hinzufügen.**

**Leistungsbeschreibung****Specifications**

|                              |                                                                                    |
|------------------------------|------------------------------------------------------------------------------------|
| <b>Product Code</b>          | XE-3066-001                                                                        |
| <b>General Description</b>   | Highly flexible, sheath can be bent/formed to suit many applications and processes |
| <b>Thermocouple Type</b>     | K                                                                                  |
| <b>Thermocouple Junction</b> | Insulated hot junction                                                             |
| <b>Probe Diameter</b>        | 6.0mm                                                                              |
| <b>Probe Length</b>          | 1000mm                                                                             |
| <b>Sheath Material</b>       | 310 stainless steel                                                                |
| <b>Pot Type</b>              | M8 x 1.0mm fine pitch threaded pot seal (200°C)                                    |
| <b>Cable Length</b>          | 100mm                                                                              |
| <b>Cable Type</b>            | PFA twin twisted                                                                   |
| <b>Core / Strands</b>        | 7/0.2mm                                                                            |
| <b>Cable Termination</b>     | Bare tails                                                                         |
| <b>Max. Temperature</b>      | 1100°C                                                                             |
| <b>Standards Met</b>         | colour coded to ANSI MC96.1                                                        |