




LABFACILITY


TEMPERATURE & PROCESS TECHNOLOGY

500 Ohm Flachschiichtdetektoren - Klasse A - 2 mm x 5 mm



Labfacility are currently multi-sourcing flat film detectors in order to ensure we can maintain a supply service to our customers without affecting the quality or functionality for the foreseeable future.

All flat film detectors supplied, although differing in appearance and packaging in some cases, will meet the specifications as published on our data sheets.



Labfacility are the UK's leading manufacturer of Temperature Sensors, Thermocouple Connectors and associated Temperature Instrumentation and stockings of Thermocouple Cables. The Company has been trading since 1971 and is ISO9001 accredited.

Labfacility beschafft derzeit Flachsichtdetektoren mehrfach, um sicherzustellen, dass wir unseren Kunden auf absehbare Zeit einen Lieferservice bieten können, ohne die Qualität oder Funktionalität zu beeinträchtigen.

Alle gelieferten Flachfilmdetektoren unterscheiden sich zwar teilweise in Aussehen und Verpackung, erfüllen aber die Spezifikationen, die auf unseren Datenblättern veröffentlicht sind.

Leistungsbeschreibung

Specifications

Product Code	XE-4630-001
Element/hot junction	Thin film construction
Element	Pt500 to IEC751
Max. Temperature	500°C
Min. Temperature	-50°C
Tolerance	Class A in accordance with IEC 60751
Dimensions	2mm Width x 5mm Length
Important Information	Resists vibration & shock