


500 Ohm Flachfilmdetektoren

Labfacility are currently multi-sourcing flat film detectors in order to ensure we can maintain a supply service to our customers without affecting the quality or functionality for the foreseeable future.

All flat film detectors supplied, although differing in appearance and packaging in some cases, will meet the specifications as published on our data sheets.



[Click here to view product](#)

Product Code	XE-4600
Element/hot junction	Thin film construction
Element	Pt500 to IEC751
Max. Temperature	+500°C
Min. Temperature	-50°C
Tolerance	Class B or A available in accordance with IEC 60751
Features #1	Resists vibration & shock