

Glimmerdüsenheizungen



[Click here to view product](#)

Product Code	XE-9500
General Description	Best quality Mica for high dielectric strength and maximum heat transfer
Element	High performance precision wound element for superior heat distribution
Cable Length	1 metre long stainless steel braided cable
Max. Temperature	Recommended for temperatures up to 300°C
Output	240V
Features #1	Full width low expansion straps
Features #2	Specially treated finish to resist oxidation and enhance thermal conductivity
Important Information	Wide range of applications including plastic process machinery, injection / blow moulding, rubber moulding, test equipment, food process industry etc