

## **ANSI Fabricated Tube Thermoelemente mit Crimpdichtung und Anschlussdraht - Typ K - 3,0 mm x 50 mm**



Labfacility are the UK's leading manufacturer of Temperature Sensors, Thermocouple Connectors and associated Temperature Instrumentation and stockings of Thermocouple Cables. The Company has been trading since 1971 and is ISO9001 accredited.

**Typische Anwendungen**

Industrielle Prozesskontrolle

Rohre oder Kanäle

Öfen und Heizung

Universell einsetzbar

**Leistungsbeschreibung****Specifications**

|                             |                                                                                        |
|-----------------------------|----------------------------------------------------------------------------------------|
| <b>Product Code</b>         | XE-7936-001                                                                            |
| <b>General Description</b>  | Fabricated Type K Thermocouple with Rigid Stainless Steel Sheath with 1 metre PFA lead |
| <b>Thermocouple Type</b>    | K                                                                                      |
| <b>Cable Length</b>         | 1M                                                                                     |
| <b>Cable Type</b>           | PFA                                                                                    |
| <b>Termination Type</b>     | Stripped Wires                                                                         |
| <b>Sheath Length (mm)</b>   | 50                                                                                     |
| <b>Sheath Diameter (mm)</b> | 3.0                                                                                    |
| <b>Max. Temperature</b>     | 250°C                                                                                  |
| <b>Min. Temperature</b>     | 75°C                                                                                   |
| <b>Tolerance</b>            | Class 1                                                                                |
| <b>Standards Met</b>        | ANSI MC96.1                                                                            |
| <b>Number of Wires</b>      | 2                                                                                      |
| <b>Series</b>               | Fabricated Tube Thermocouple                                                           |