






## Typ VX (KCB) PVC Isoliertes Flachpaar-Thermoelementkabel/-Draht (IEC) für den Einsatz mit Typ-K-Thermoelementen 13/0,2 mm



—K—J—T—N—RCA—KCB



Labfacility are the UK's leading manufacturer of Temperature Sensors, Thermocouple Connectors and associated Temperature Instrumentation and stockings of Thermocouple Cables. The Company has been trading since 1971 and is ISO9001 accredited.

**Technische Daten****Specifications**

|                                                         |                                                                                         |
|---------------------------------------------------------|-----------------------------------------------------------------------------------------|
| <b>General Description</b>                              | Good general purpose insulation for 'light' environments. Waterproof and very flexible. |
| <b>Cable Length</b>                                     | 10, 25, 50, 100, 200m                                                                   |
| <b>Cable Type</b>                                       | Flat pair construction                                                                  |
| <b>Core / Strands</b>                                   | 13/0.2mm                                                                                |
| <b>Conductor Cross Section 13/0.2 (mm<sup>2</sup>)</b>  | 0.408                                                                                   |
| <b>Outer Colour</b>                                     | Green                                                                                   |
| <b>+ Colour</b>                                         | Green                                                                                   |
| <b>- Colour</b>                                         | White                                                                                   |
| <b>Insulation Material</b>                              | PVC Insulated                                                                           |
| <b>Loop Resistance 13/0.2 (Ohms per combined metre)</b> | 1.2                                                                                     |
| <b>Max. Temperature</b>                                 | 105°C                                                                                   |
| <b>Min. Temperature</b>                                 | -10°C                                                                                   |
| <b>+ Conductor</b>                                      | Copper                                                                                  |
| <b>- Conductor</b>                                      | Constantan                                                                              |
| <b>Screen</b>                                           | No                                                                                      |
| <b>Standards Met</b>                                    | Colour code (cores & jacket) to IEC-584-3                                               |
| <b>Termination Type</b>                                 | VX (KCB)                                                                                |



|           |         |
|-----------|---------|
| Tolerance | Class 2 |
|-----------|---------|