




LABFACILITY

TEMPERATURE & PROCESS TECHNOLOGY

Typ K Glasfaser-isoliertes Flachpaar-Thermoelement-Kabel / Draht (IEC) 7/0,2 mm Strang



Labfacility are the UK's leading manufacturer of Temperature Sensors, Thermocouple Connectors and associated Temperature Instrumentation and stockings of Thermocouple Cables. The Company has been trading since 1971 and is ISO9001 accredited.

Glasfaserisolierte Flachpaarkonstruktion, Leiter flach verlegt, Glasfaser komplett mit Glasfaser isoliert, durchgehend mit Silikonlack lackiert. Gute Temperaturbestndigkeit, aber nicht geeignet, wo Flssigkeiten vorhanden sind.

Technische Daten

Specifications

General Description	Good temperature range but will not prevent ingress of fluids. Fairly flexible but does not provide good mechanical protection.
Cable Length	10m, 25m, 50m, 100m, 200m
Cable Type	Flat pair cable
Core / Strands	7/0.2mm
Conductor Cross Section 7/0.2 (mm²)	0.219
Outer Colour	Green & White
+ Colour	Green
- Colour	White
Drain Wire	No
Insulation Material	Glassfibre insulated
Loop Resistance 7/0.2 (Ohms per combined metre)	4.5
Max. Temperature	+350°C (short periods up to 400°C)
Min. Temperature	-60°C
+ Conductor	Nickel Chromium
- Conductor	Nickel Aluminium
Screen	No



LABFACILITY

TEMPERATURE & PROCESS TECHNOLOGY

Standards Met	Colour code (cores & jacket) to IEC-584-3
Thermocouple Type	K
Tolerance	Class 2